



Predstavljamo vam

# ŠARKE

## LAGER KOLEKCIJA

BLUM je standard kvaliteta svojih proizvoda postavio na veoma visok nivo. Oni ne ispunjavaju naša očekivanja, oni ta očekivanja uvek nadmašuju.



Nameštaj Darex Home



#darex\_home

### DAREX LAGER KOLEKCIJA - OKOV >

Brojni su razlozi da se odlučite za BLUM-ove šarke. Visoki kvalitet, jednostavna i brza montaža i demontaža, obiman program, brojna specifična rešenja i atraktivan dizajn, neće vas ostaviti dugo u nedoumici.

Pogledajte našu ponudu BLUM šarki. Učitajte QR code sa desne strane!



## CLIP-TOP STANDARD



**544817**  
**Šarka telo Clip-Top 100°**  
ravna sa oprugom

**544825**  
**Šarka telo Clip-Top 100°**  
polukoleno sa oprugom

**545015**  
**Šarka telo Clip-Top 100°**  
koleno sa oprugom

ŠARKA Clip-Top 100°  
- sa oprugom



**548634**  
**Šarka telo Clip-Top 100°**  
ravna bez opruge

**548626**  
**Šarka telo Clip-Top 100°**  
polukoleno bez opruge

**548618**  
**Šarka telo Clip-Top 100°**  
koleno bez opruge

ŠARKA Clip-Top 100°  
- bez opruge



**560898**  
**Šarka telo Clip-Top 110°**  
ravna sa oprugom

**560901**  
**Šarka telo Clip-Top 110°**  
polukoleno sa oprugom

**560928**  
**Šarka telo Clip-Top 110°**  
koleno sa oprugom

ŠARKA Clip-Top 110°  
- sa oprugom



**143230**  
**Šarka Inserta Clip 110°**  
ravna sa oprugom

**143231**  
**Šarka Inserta Clip 110°**  
polukoleno sa oprugom

**143232**  
**Šarka Inserta Clip 110°**  
koleno sa oprugom

ŠARKA Inserta Clip-Top 110°  
- sa oprugom



**143250**  
**Šarka Inserta Clip 110°**  
ravna bez opruge

**143251**  
**Šarka Inserta Clip 110°**  
polukoleno bez opruge

**143270**  
**Šarka Inserta Clip 110°**  
koleno bez opruge

ŠARKA Inserta Clip-Top 110°  
- bez opruge



**184390**  
**Šarka telo Clip-Top 110°**  
ravna sa oprugom - Tanki Front

**184410**  
**Šarka telo Clip-Top 110°**  
ravna bez opruge - Tanki Front

ŠARKA Clip-Top 110°  
- tanki front



PLOČICA za Clip-Top  
- univerzalna

**545260**  
Pločica 0 za Clip-Top 8,5mm  
- univerzalna  
**548413**  
Pločica 3 za Clip-Top 11,5mm  
- univerzalna



PLOČICA za Clip-Top  
- ekscentarska unakrsna

**1254421**  
Pločica 0 za Clip-Top 8,5mm  
- ekscentarska unakrsna  
**1254448**  
Pločica 3 za Clip-Top 11,5mm  
- ekscentarska unakrsna



PLOČICA za Clip-Top  
- ekscentarska unakrsna ONIX

**184430**  
Pločica 0 za Clip-Top 8,5mm  
- ekscentarska unakrsna ONIX  
**184450**  
Pločica 3 za Clip-Top 11,5mm  
- ekscentarska unakrsna ONIX



PLOČICA za Clip-Top  
- unakrsna sa eurovijkom

**170250**  
Pločica 0 za Clip-Top 8,5mm  
- unakrsna sa eurovijkom  
**173670**  
Pločica 3 za Clip-Top 11,5mm  
- unakrsna sa eurovijkom



PLOČICA za Clip-Top  
- ekscentarska ravna

**547433**  
Pločica 0 za Clip-Top 8,5mm  
- ekscentarska ravna  
**173671**  
Pločica 3 za Clip-Top 11,5mm  
- ekscentarska ravna



PLOČICA za Clip-Top  
- ekscentarska ravna ONIX

**177790**  
Pločica 0 za Clip-Top 8,5mm  
- ekscentarska ravna ONIX  
**177810**  
Pločica 3 za Clip-Top 11,5mm  
- ekscentarska ravna ONIX



PLOČICA Inserta za Clip-Top  
- ekscentarska

**143271**  
Pločica Inserta 0  
za Clip-Top 8,5mm  
**143290**  
Pločica Inserta 3  
za Clip-Top 11,5mm



UGAONI KLIN za pločicu

**173672**  
Ugaoni klin za pločicu  
H=3mm +5°  
**173673**  
Ugaoni klin za pločicu  
H=6mm +5°  
**173674**  
Ugaoni klin za pločicu  
H=6mm -5°



POKLOPAC sa i bez otiska

**544639**  
Poklopac sa otiskom za  
Clip-Top 100° - ravnu  
**545287**  
Poklopac bez otiska za  
Clip-Top 100° - polukol/koleno  
**544221**  
Poklopac sa otiskom za  
Clip-Top 120° - ravnu  
**560871**  
Poklopac sa otiskom za  
Clip-Top 120° - polukoleno



POKLOPAC sa otiskom

**184470**  
Poklopac sa otiskom za  
Clip-Top 100° - ravnu ONIX



**560863**  
**Poklopac lonca**  
za šarku Blumotion

POKLOPAC lonca



**184472**  
**Poklopac lonca**  
za šarku Blumotion ONIX

POKLOPAC lonca ONIX



**544612**  
**Usporivač Blumotion 973A**  
za Clip-Top 100/120° - ravnu  
**544833**  
**Usporivač Blumotion 973A**  
za Clip-Top 100° - polukoleno  
**545023**  
**Usporivač Blumotion 973A**  
za Clip-Top 100° - koleno

USPORIVAČ Blumotion 973A



**173675**  
**Usporivač Blumotion 970**  
štipičasti

USPORIVAČ Blumotion 970



**173676**  
**Adapter za Blumotion 970**  
- ravni  
**173677**  
**Adapter za Blumotion 970**  
- krstasti

ADAPTER za Blumotion 970



**1125052**  
**Tip-On za vrata**  
- kratka verzija - SIVI  
**1125060**  
**Tip-On za vrata**  
- duga verzija - SIVI  
**188930**  
**Tip-On za vrata**  
- kratka verzija - BELI  
**188950**  
**Tip-On za vrata**  
- duga verzija - BELI

TIP-ON



**1125079**  
**Tip-On Adapter za vrata**  
- kratka verzija - SIVI  
**1125087**  
**Tip-On Adapter za vrata**  
- duga verzija - SIVI  
**188970**  
**Tip-On Adapter za vrata**  
- kratka verzija - BELI  
**188990**  
**Tip-On Adapter za vrata**  
- duga verzija - BELI

TIP-ON

## CLIP-TOP UGAONE



**545228**  
**Šarka telo Clip-Top**  
- ugaona sa oprugom

ŠARKA ugaona



**173682**  
**Šarka telo Clip-Top**  
+45° bez opruge

ŠARKA +45°



ŠARKA 95°

**545066**  
Šarka telo Clip-Top  
+95° sa oprugom  
**173683**  
Šarka telo Clip-Top  
+95° bez opruge



ŠARKA 155°

**173684**  
Šarka telo Clip-Top  
155° ravna sa oprugom - [Nova](#)  
**173685**  
Šarka telo Clip-Top  
155° ravna bez opruge - [Nova](#)



ŠARKA 170°

**545058**  
Šarka telo Clip-Top  
170° sa oprugom  
**174354**  
Šarka telo Clip-Top  
170° bez opruge



USPORIVAČ Blumotion 973A

**173686**  
Usporivač Blumotion 973A  
za Clip-Top 170°

## CLIP-TOP BLUMOTION



ŠARKA Blumotion 110°  
- sa oprugom

**560812**  
Šarka telo Blumotion 110°  
- ravna sa oprugom  
**560820**  
Šarka telo Blumotion 110°  
- polukoleno sa oprugom  
**560839**  
Šarka telo Blumotion 110°  
- koleno sa oprugom



ŠARKA Blumotion 110°  
- sa oprugom ONIX

**177830**  
Šarka telo Blumotion 110°  
- ravna sa oprugom ONIX  
**177850**  
Šarka telo Blumotion 110°  
- polukoleno sa oprugom ONIX  
**177870**  
Šarka telo Blumotion 110°  
- koleno sa oprugom ONIX



ŠARKA Blumotion 110°  
- sa oprugom Tanki Front

**184490**  
Šarka telo Blumotion 110°  
- ravna sa oprugom Tanki Front



ŠARKA Blumotion 110°  
- sa oprugom Tanki Front

**184510**  
Šarka telo Blumotion 110°  
- ravna sa oprugom Tanki Front  
ONIX



ŠARKA Blumotion 110°  
- sa oprugom INSERTA

**174350**  
Šarka telo Blumotion 110°  
- ravna sa oprugom - Inserta  
**174352**  
Šarka telo Blumotion 110°  
- polukoleno sa oprugom - Inserta  
**174353**  
Šarka telo Blumotion 110°  
- koleno sa oprugom - Inserta



ŠARKA Blumotion +45°

**173678**  
Šarka telo Blumotion  
Clip-Top +45° preklapajuća



**177750**  
**Šarka telo Blumotion**  
**Clip-Top +45°**

ŠARKA Blumotion +45°



**173679**  
**Šarka telo Blumotion**  
**Clip-Top 95°**  
**177890**  
**Šarka telo Blumotion**  
**Clip-Top 95° ONIX**

ŠARKA Blumotion 95°



**177770**  
**Šarka telo Blumotion**  
**Clip-Top 95° - preklapajuća**

ŠARKA Blumotion 95°



**173680**  
**Šarka telo Blumotion**  
**Clip-Top 155° ravna**  
**177910**  
**Šarka telo Blumotion**  
**Clip-Top 155° ravna ONIX**

ŠARKA Blumotion 155°

## ŠARKA ZA STAKLO



**143313**  
**Šarka Crystallo**  
- sa oprugom  
**143314**  
**Šarka Crystallo**  
- bez opruge

ŠARKA Crystallo



**143315**  
**Pločica Crystallo**  
za lonac mat-niklovana

PLOČICA Crystallo





**184530**  
**Poklopac univerzalni**  
za Crystallo

POKLOPAC za Crystallo



# UPUTSTVO ZA ŠARKE, ZA TANKA VRATA

## Overlay application





F Gap

## Dual application



F Gap

## Inset application



Set mounting plate back by door thickness +1.5 mm


F Gap

## Fixing position

MD	Front overlay FA (mm)																	
	-3.5	-3	-2.5	-2	-1.5	-1	2.5	4	5.5	7	8.5	10	11.5	13	14.5	16	17.5	19
0	23.5	24	24.5	25	25.5	26	29.5	31	32.5	34	35.5	37	38.5	40	41.5	43	44.5	46
3	26.5	27	27.5	28	28.5	29	32.5	34	35.5	37	38.5	40	41.5	43	44.5	46		
6	29.5	30	30.5	31	31.5	32	35.5	37	38.5	40	41.5	43	44.5	46				
9	32.5	33	33.5	34	34.5	35	38.5	40	41.5	43	44.5	46						

MD Mounting plate spacing (mm)

## Fixing position




B Fixing position

$B = FA + 27$  mm


FA Front overlay

\* Stone and ceramic +0.2/-0.1 mm




B Fixing position


## Adjustment



Max. ±3.0 mm  
See mounting plates




±2.0 mm



+3.0 mm  
-2.0 mm

## Drilling depth



BT Drilling depth

## Mounting plate spacing MD – cabinet hinge side on the wall

SWD (mm)	Front thickness FD (mm)						
	8	9	10	11	12	13	14
15							
16							
17							
18							
19							
20							


SWD Cabinet side panel thickness

Mounting plate spacing MD 0 mm possible


Mounting plate spacing MD 3 mm required

Mounting plate spacing MD 6 mm required


# TEHNIČKE KARAKTERISTIKE










<p>H = 8.5 D = 0</p>	<p>H = 11.5 D = 3</p>	
<b>FA</b>	<b>FA</b>	<b>TB</b>
14	11	3
15	12	4
16	13	5
17	14	6



<p>H = 8.5 D = 0</p>	<p>H = 11.5 D = 3</p>	
<b>FA</b>	<b>FA</b>	<b>TB</b>
4.5	1.5	3
5.5	2.5	4
6.5	3.5	5
7.5	4.5	6









<p>H = 8.5 D = 0</p>	<p>H = 11.5 D = 3</p>	
<b>FA</b>	<b>FA</b>	<b>TB</b>
-4	-7	3
-3	-6	4
-2	-5	5
-1	-4	6









# UPUTSTVO ZA ŠTELOVANJE









## Graničnik **ugla**



## Clip Top **BLUMOTION**





Prikaz proizvoda na fotografijama može da ne odgovara u potpunosti originalnom uzorku.  
Za originalan uzorak proizvoda obratite se vashem Darex prodavcu.